

Alternate Catalog No. SU201MR-K40 n° de catalogue 2CDS271347R0557

Description: MCB SU200MR RTT 1P K 40A BCP

UPC No 4016779956611

Accueil > Modular DIN Rail Products > Mini Circuit breakers

SU201MR-K40 MCB K-Char., 10kA, 40A, 1P, RTT UL 489, Ring Cable Lug



Image représentative

Descripteurs

Catégorie	Mini Circuit breakers
-----------	-----------------------

Spécifications

Interrupting Rating acc. to UL489	(240 V AC) 10 kA (48 V DC) 10 kA
Number of Poles	1
Power Loss	at Rated Operating Conditions per Pole 4.5 W
Product Main Type	SU200MR
Rated Current	40 A
Rated Voltage (V)	(240 V AC) (48 V DC)
Tripping Characteristic	K