



**Alternate Catalog No. SU201MR-K50**  
**Catalog No. 2CDS271347R0577**

**Description: MCB SU200MR RTT 1P K 50A BCP**

**UPC No 4016779956635**

**Home > Modular DIN Rail Products > Mini Circuit breakers**

SU201MR-K50 MCB K-Char., 10kA, 50A, 1P, RTT UL 489, Ring Cable Lug

**Descriptors**

Category	Mini Circuit breakers
----------	-----------------------

**Specifications**

Interrupting Rating acc. to UL489	(240 V AC) 10 kA (48 V DC) 10 kA
Number of Poles	1
Power Loss	at Rated Operating Conditions per Pole 4.5 W
Product Main Type	SU200MR
Rated Current	50 A
Rated Voltage (V)	(240 V AC) (48 V DC)
Tripping Characteristic	K