

**Alternate Catalog No. SU202M-C4**  
**Typ 2CDS272337R0044**
**Opis: UL489 MCB 2P C 4A 480/277**
**UPC No 4016779931021**
**Strona główna > Modular DIN Rail Products > Mini Circuit breakers**

SU202M-C4 Miniature Circuit Breaker C-Char., 10kA, 4A, 2P UL489



Reprezentatywny obraz

**Deskryptory**

Category	Mini Circuit breakers
----------	-----------------------

**Specyfikacje**

Interrupting Rating acc. to UL489	(480Y / 277 V AC) 10 kA (96 V DC) 10 kA
Number of Poles	2
Power Loss	3,6 W at Rated Operating Conditions per Pole 1,8 W
Product Main Type	SU200M
Rated Current	4 A
Rated Ultimate Short-Circuit Breaking Capacity	(400 V AC) 15 kA
Napięcie znamionowe	(480Y / 277 V AC) (96 V DC)
Normy	CSA 22.2 No. 5 IEC/EN 60947-2 UL 489
Tripping Characteristic	C