

**Alternate Catalog No. SU202M-K0.2**  
**Catalog No. 2CDS272337R0087**

**Description:** UL489 MCB 2P K 0.2A 480/277

**UPC No** 4016779932585

**Home > Modular DIN Rail Products > Mini Circuit breakers**

SU202M-K0,2 Miniature Circuit Breaker K-Char., 10kA, 0,2A, 2P UL489



Representative Image

### Descriptors

Category	Mini Circuit breakers
----------	-----------------------

### Specifications

Interrupting Rating acc. to UL489	(480Y / 277 V AC) 10 kA (96 V DC) 10 kA
Number of Poles	2
Power Loss	3,4 W at Rated Operating Conditions per Pole 1,7 W
Product Main Type	SU200M
Rated Current	0.20 A
Rated Ultimate Short-Circuit Breaking Capacity	(400 V AC) 15 kA
Rated Voltage (V)	(480Y / 277 V AC) (96 V DC)
Standards	CSA 22.2 No. 5 IEC/EN 60947-2 UL 489
Tripping Characteristic	K