



**Alternate Catalog No. SU202M-C20**  
**Catalog No. 2CDS272337R0204**

**Description:** UL489 MCB 2P C 20A 480/277

**UPC No** 4016779931113

**Home > Modular DIN Rail Products > Mini Circuit breakers**

SU202M-C20 Miniature Circuit Breaker C-Char., 10kA, 20A, 2P UL489

**Descriptors**

Category	Mini Circuit breakers
----------	-----------------------

**Specifications**

Interrupting Rating acc. to UL489	(480Y / 277 V AC) 10 kA (96 V DC) 10 kA
Number of Poles	2
Power Loss	5 W at Rated Operating Conditions per Pole 2,5 W
Product Main Type	SU200M
Rated Current	20 A
Rated Ultimate Short-Circuit Breaking Capacity	(400 V AC) 15 kA
Rated Voltage (V)	(480Y / 277 V AC) (96 V DC)
Standards	CSA 22.2 No. 5 IEC/EN 60947-2 UL 489
Tripping Characteristic	C