



Representative Image

Alternate Catalog No. SU202M-Z2
Catalog No. 2CDS272337R0278

Description: UL489 MCB 2P Z 2A 480/277

UPC No 4016779933100

Home > Modular DIN Rail Products > Mini Circuit breakers

SU202M-Z2 Miniature Circuit Breaker Z-Char., 10kA, 2A, 2P UL489

Descriptors

| | |
|----------|-----------------------|
| Category | Mini Circuit breakers |
|----------|-----------------------|

Specifications

| | |
|--|---|
| Interrupting Rating acc. to UL489 | (480Y / 277 V AC) 10 kA (96 V DC) 10 kA |
| Number of Poles | 2 |
| Power Loss | 5,2 W at Rated Operating Conditions per Pole 2,6 W |
| Product Main Type | SU200M |
| Rated Current | 2 A |
| Rated Ultimate Short-Circuit Breaking Capacity | (400 V AC) 15 kA |
| Rated Voltage (V) | (480Y / 277 V AC) (96 V DC) |
| Standards | CSA 22.2 No. 5 IEC/EN 60947-2 UL 489 |
| Tripping Characteristic | Z |