

Representative Image

# Alternate Catalog No. SU202M-C30
# Catalog No. 2CDS272337R0304

**Description: UL489 MCB 2P C 30A 480/277**

**UPC No 4016779931137**

**Home > Modular DIN Rail Products > Mini Circuit breakers**

SU202M-C30 Miniature Circuit Breaker C-Char., 10kA, 30A, 2P UL489

## Descriptors

| | |
|---|---|
| Category | Mini Circuit breakers |

## Specifications

| | |
|---|---|
| Interrupting Rating acc. to UL489 | (480Y / 277 V AC) 10 kA<br>(96 V DC) 10 kA |
| Number of Poles | 2 |
| Power Loss | 7 W<br>at Rated Operating Conditions per Pole 3,5 W |
| Product Main Type | SU200M |
| Rated Current | 30 A |
| Rated Ultimate Short-Circuit Breaking Capacity | (400 V AC) 15 kA |
| Rated Voltage (V) | (480Y / 277 V AC)<br>(96 V DC) |
| Standards | CSA 22.2 No. 5<br>IEC/EN 60947-2<br>UL 489 |
| Tripping Characteristic | C |