



Representative Image

**Alternate Catalog No. SU202M-K5**  
**Catalog No. 2CDS272337R0357**

**Description:** UL489 MCB 2P K 5A 480/277

**UPC No** 4016779932677

**Home > Modular DIN Rail Products > Mini Circuit breakers**

SU202M-K5 Miniature Circuit Breaker K-Char., 10kA, 5A, 2P UL489

**Descriptors**

|          |                       |
|----------|-----------------------|
| Category | Mini Circuit breakers |
|----------|-----------------------|

**Specifications**

|  |   |
|--|---|
| Interrupting Rating acc. to UL489              | (480Y / 277 V AC) 10 kA<br>(96 V DC) 10 kA            |
| Number of Poles                                | 2   |
| Power Loss                                     | 2,6 W<br>at Rated Operating Conditions per Pole 1,3 W |
| Product Main Type                              | SU200M  |
| Rated Current                                  | 5 A   |
| Rated Ultimate Short-Circuit Breaking Capacity | (400 V AC) 15 kA                                      |
| Rated Voltage (V)                              | (480Y / 277 V AC)<br>(96 V DC)                        |
| Standards                                      | CSA 22.2 No. 5<br>IEC/EN 60947-2<br>UL 489            |
| Tripping Characteristic                        | K   |