

**Alternate Catalog No. SU202M-K6**  
**n° de catalogue 2CDS272337R0377**
**Description: UL489 MCB 2P K 6A 480/277**
**UPC No 4016779932684**
**Accueil > Modular DIN Rail Products > Mini Circuit breakers**

SU202M-K6 Miniature Circuit Breaker K-Char., 10kA, 6A, 2P UL489



Image représentative

**Descripteurs**

Catégorie	Mini Circuit breakers
-----------	-----------------------

**Spécifications**

Interrupting Rating acc. to UL489	(480Y / 277 V AC) 10 kA (96 V DC) 10 kA
Number of Poles	2
Power Loss	4 W at Rated Operating Conditions per Pole 2,0 W
Product Main Type	SU200M
Rated Current	6 A
Rated Ultimate Short-Circuit Breaking Capacity	(400 V AC) 15 kA
Rated Voltage (V)	(480Y / 277 V AC) (96 V DC)
Standards	CSA 22.2 No. 5 IEC/EN 60947-2 UL 489
Tripping Characteristic	K