



Representative Image

**Alternate Catalog No. SU202M-K40**  
**Catalog No. 2CDS272337R0557**

**Description: UL489 MCB 2P K 40A 240**

**UPC No 4016779932806**

**Home > Modular DIN Rail Products > Mini Circuit breakers**

SU202M-K40 Miniature Circuit Breaker K-Char., 10kA, 40A, 2P UL489

**Descriptors**

Category	Mini Circuit breakers
----------	-----------------------

**Specifications**

Interrupting Rating acc. to UL489	(240 V AC) 10 kA (96 V DC) 10 kA
Number of Poles	2
Power Loss	9 W at Rated Operating Conditions per Pole 4,5 W
Product Main Type	SU200M
Rated Current	40 A
Rated Ultimate Short-Circuit Breaking Capacity	(400 V AC) 15 kA
Rated Voltage (V)	(240 V AC) (96 V DC)
Standards	CSA 22.2 No. 5 IEC/EN 60947-2 UL 489
Tripping Characteristic	K