



**Alternate Catalog No. SU202MR-K0.2**  
**Catalog No. 2CDS272347R0087**

**Description:** MCB SU200MR RTT 2P K 0.2A BCP

**UPC No** 4016779957175

**Home > Modular DIN Rail Products > Mini Circuit breakers**

SU202MR-K0.2 MCB K-Char., 10kA, 0.2A, 2P, RTT UL 489, Ring Cable Lug

**Descriptors**

Category	Mini Circuit breakers
----------	-----------------------

**Specifications**

Interrupting Rating acc. to UL489	(480Y / 277 V AC) 10 kA (96 V DC) 10 kA
Number of Poles	2
Power Loss	at Rated Operating Conditions per Pole 1.7 W
Product Main Type	SU200MR
Rated Current	0.20 A
Rated Voltage (V)	(480Y / 277 V AC) (96 V DC)
Tripping Characteristic	K