

## Alternate Catalog No. SU202MR-K1.6
## Catalog No. 2CDS272347R0257

**Description: MCB SU200MR RTT 2P K 1.6A BCP**

**UPC No 4016779957274**

**Home > Modular DIN Rail Products > Mini Circuit breakers**

SU202MR-K1,6 MCB K-Char., 10kA, 1,6A, 2P, RTT UL 489, Ring Cable Lug

### Descriptors

| | |
|---|---|
| Category | Mini Circuit breakers |

### Specifications

| | |
|---|---|
| Interrupting Rating acc. to UL489 | (480Y / 277 V AC) 10 kA<br>(96 V DC) 10 kA |
| Number of Poles | 2 |
| Power Loss | at Rated Operating Conditions per Pole 1.8 W |
| Product Main Type | SU200MR |
| Rated Current | 1.6 A |
| Rated Voltage (V) | (480Y / 277 V AC)<br>(96 V DC) |
| Tripping Characteristic | K |