

Representative Image

Alternate Catalog No. SU202MR-K4
Catalog No. 2CDS272347R0337

Description: MCB SU200MR RTT 2P K 4A BCP

UPC No 4016779957335

Home > Modular DIN Rail Products > Mini Circuit breakers

SU202MR-K4 MCB K-Char., 10kA, 4A, 2P, RTT UL 489, Ring Cable Lug

Descriptors

Category	Mini Circuit breakers

Specifications

Interrupting Rating acc. to UL489	(480Y / 277 V AC) 10 kA (96 V DC) 10 kA
Number of Poles	2
Power Loss	at Rated Operating Conditions per Pole 1.8 W
Product Main Type	SU200MR
Rated Current	4 A
Rated Voltage (V)	(480Y / 277 V AC) (96 V DC)
Tripping Characteristic	K