

Representative Image

# Alternate Catalog No. SU202MR-K5
# Catalog No. 2CDS272347R0357

**Description: MCB SU200MR RTT 2P K 5A BCP**

**UPC No 4016779957359**

**Home > Modular DIN Rail Products > Mini Circuit breakers**

SU202MR-K5 MCB K-Char., 10kA, 5A, 2P, RTT UL 489, Ring Cable Lug

## Descriptors

| | |
|---|---|
| Category | Mini Circuit breakers |

## Specifications

| | |
|---|---|
| Interrupting Rating acc. to UL489 | (480Y / 277 V AC) 10 kA<br>(96 V DC) 10 kA |
| Number of Poles | 2 |
| Power Loss | at Rated Operating Conditions per Pole 1.3 W |
| Product Main Type | SU200MR |
| Rated Current | 5 A |
| Rated Voltage (V) | (480Y / 277 V AC)<br>(96 V DC) |
| Tripping Characteristic | K |