



Alternate Catalog No. SU202MR-K10
Catalog No. 2CDS272347R0427

Description: MCB SU200MR RTT 2P K 10.6A BCP

UPC No 4016779957410

Home > Modular DIN Rail Products > Mini Circuit breakers

SU202MR-K10 MCB K-Char., 10kA, 10A, 2P, RTT UL 489, Ring Cable Lug

Descriptors

Category	Mini Circuit breakers
----------	-----------------------

Specifications

Interrupting Rating acc. to UL489	(480Y / 277 V AC) 10 kA (96 V DC) 10 kA
Number of Poles	2
Power Loss	at Rated Operating Conditions per Pole 2.1 W
Product Main Type	SU200MR
Rated Current	10 A
Rated Voltage (V)	(480Y / 277 V AC) (96 V DC)
Tripping Characteristic	K