



Alternate Catalog No. SU202MR-K63
Catalog No. 2CDS272347R0607

Description: MCB SU200MR RTT 2P K 63A BCP

UPC No 4016779957656

Home > Modular DIN Rail Products > Mini Circuit breakers

SU202MR-K63 MCB K-Char., 10kA, 63A, 2P, RTT UL 489, Ring Cable Lug

Descriptors

| | |
|----------|-----------------------|
| Category | Mini Circuit breakers |
|----------|-----------------------|

Specifications

| | |
|-----------------------------------|--|
| Interrupting Rating acc. to UL489 | (240 V AC) 10 kA (96 V DC) 10 kA |
| Number of Poles | 2 |
| Power Loss | at Rated Operating Conditions per Pole 5.4 W |
| Product Main Type | SU200MR |
| Rated Current | 63 A |
| Rated Voltage (V) | (240 V AC) (96 V DC) |
| Tripping Characteristic | K |