



Alternate Catalog No. ST203M-D32
Catalog No. 2CDS273334R0321

Description: MCB ST200M 3P D 32A UL1077

UPC No 4016779024303

Home > Modular DIN Rail Products > Mini Circuit breakers

ST203M-D32 Miniature Circuit Breaker ST203M-D32 Miniature Circuit Breaker D-Char., 10kA, 32A, 3P

Descriptors

| | |
|----------|-----------------------|
| Category | Mini Circuit breakers |
|----------|-----------------------|

Specifications

| | |
|------------------------------------|--|
| Interrupting Rating acc. to UL1077 | (240 V AC) 10 kA (480Y / 277 VAC) 10 kA (125 V DC) 10 kA |
| Number of Poles | 3 |
| Product Main Type | ST200M |
| Rated Current | 32 A |
| Rated Voltage (V) | (240 V AC) (125 V DC) |
| Tripping Characteristic | D |