



**Alternate Catalog No. ST203M-D40**  
**Catalog No. 2CDS273334R0401**

**Description: MCB ST200M 3P D 40A UL1077**

**UPC No 4016779024525**

**Home > Modular DIN Rail Products > Mini Circuit breakers**

ST203M-D40 Miniature Circuit Breaker ST203M-D40 Miniature Circuit Breaker D-Char., 5kA, 40A, 3P

**Descriptors**

Category	Mini Circuit breakers
----------	-----------------------

**Specifications**

Interrupting Rating acc. to UL1077	(240 V AC) 10 kA (480Y / 277 VAC) 5 kA (125 V DC) 10 kA
Number of Poles	3
Product Main Type	ST200M
Rated Current	40 A
Rated Voltage (V)	(240 V AC) (125 V DC)
Tripping Characteristic	D