



Representative Image

Alternate Catalog No. SU203M-C60
Catalog No. 2CDS273337R0604

Description: UL489 MCB 3P C 60A 240

UPC No 4016779931410

Home > Modular DIN Rail Products > Mini Circuit breakers

SU203M-C60 Miniature Circuit Breaker C-Char., 10kA, 60A, 3P UL489

Descriptors

| | |
|----------|-----------------------|
| Category | Mini Circuit breakers |
|----------|-----------------------|

Specifications

| | |
|--|--|
| Interrupting Rating acc. to UL489 | (240 V AC) 10 kA (96 V DC) 10 kA |
| Number of Poles | 3 |
| Power Loss | 14,7 W at Rated Operating Conditions per Pole 4,9 W |
| Product Main Type | SU200M |
| Rated Current | 60 A |
| Rated Ultimate Short-Circuit Breaking Capacity | (400 V AC) 15 kA |
| Rated Voltage (V) | (240 V AC) (96 V DC) |
| Standards | CSA 22.2 No. 5 IEC/EN 60947-2 UL 489 |
| Tripping Characteristic | C |