

**Alternate Catalog No. SU203M-K63**  
**Catalog No. 2CDS273337R0607**

**Description:** UL489 MCB 3P K 63A 240

**UPC No** 4016779930475

**Home > Modular DIN Rail Products > Mini Circuit breakers**

SU203M-K63 Miniature Circuit Breaker K-Char., 10kA, 63A, 3P UL489



Representative Image

**Descriptors**

Category	Mini Circuit breakers
----------	-----------------------

**Specifications**

Interrupting Rating acc. to UL489	(240 V AC) 10 kA (96 V DC) 10 kA
Number of Poles	3
Power Loss	16,2 W at Rated Operating Conditions per Pole 5,4 W
Product Main Type	SU200M
Rated Current	63 A
Rated Ultimate Short-Circuit Breaking Capacity	(400 V AC) 15 kA
Rated Voltage (V)	(240 V AC) (96 V DC)
Standards	CSA 22.2 No. 5 IEC/EN 60947-2 UL 489
Tripping Characteristic	K