

Representative Image

Alternate Catalog No. SU203MR-K0.3
Catalog No. 2CDS273347R0117

Description: MCB SU200MR RTT 3P K 0.3A BCP

UPC No 4016779958196

Home > Modular DIN Rail Products > Mini Circuit breakers

SU203MR-K0.3 MCB K-Char., 10kA, 0.3A, 3P, RTT UL 489, Ring Cable Lug

Descriptors

Category	Mini Circuit breakers

Specifications

Interrupting Rating acc. to UL489	(480Y / 277 V AC) 10 kA (96 V DC) 10 kA
Number of Poles	3
Power Loss	at Rated Operating Conditions per Pole 1.7 W
Product Main Type	SU200MR
Rated Current	0.30 A
Rated Voltage (V)	(480Y / 277 V AC) (96 V DC)
Tripping Characteristic	K