

## Alternate Catalog No. SU203MR-K0.75
## Catalog No. 2CDS273347R0187

**Description: MCB SU200MR RTT 3P K 0.75A BCP**

**UPC No 4016779958233**

**Home > Modular DIN Rail Products > Mini Circuit breakers**

SU203MR-K0.75 MCB K-Char., 10kA, 0.75A, 3P, RTT UL 489, Ring Cable Lug

### Descriptors

| | |
|---|---|
| Category | Mini Circuit breakers |

### Specifications

| | |
|---|---|
| Interrupting Rating acc. to UL489 | (480Y / 277 V AC) 10 kA<br>(96 V DC) 10 kA |
| Number of Poles | 3 |
| Power Loss | at Rated Operating Conditions per Pole 1.4 W |
| Product Main Type | SU200MR |
| Rated Current | 0.75 A |
| Rated Voltage (V) | (480Y / 277 V AC)<br>(96 V DC) |
| Tripping Characteristic | K |