



**Alternate Catalog No. SU203MR-K15**  
**Catalog No. 2CDS273347R0457**

**Description:** MCB SU200MR RTT 3P K 15A BCP

**UPC No** 4016779958455

**Home > Modular DIN Rail Products > Mini Circuit breakers**

SU203MR-K15 MCB K-Char., 10kA, 15A, 3P, RTT UL 489, Ring Cable Lug

**Descriptors**

Category	Mini Circuit breakers
----------	-----------------------

**Specifications**

Interrupting Rating acc. to UL489	(480Y / 277 V AC) 10 kA (96 V DC) 10 kA
Number of Poles	3
Power Loss	at Rated Operating Conditions per Pole 2.4 W
Product Main Type	SU200MR
Rated Current	15 A
Rated Voltage (V)	(480Y / 277 V AC) (96 V DC)
Tripping Characteristic	K