



Representative Image

Alternate Catalog No. SU204M-C16
Catalog No. 2CDS274337R0164

Description: UL489 MCB 4P C 16A 480/277

UPC No 4016779931564

Home > Modular DIN Rail Products > Mini Circuit breakers

SU204M-C16 Miniature Circuit Breaker C-Char., 10kA, 16A, 4P UL489

Descriptors

Category	Mini Circuit breakers
----------	-----------------------

Specifications

Interrupting Rating acc. to UL489	(480Y / 277 V AC) 10 kA (96 V DC) 10 kA
Number of Poles	4
Power Loss	10 W at Rated Operating Conditions per Pole 2,5 W
Product Main Type	SU200M
Rated Current	16 A
Rated Ultimate Short-Circuit Breaking Capacity	(400 V AC) 15 kA
Rated Voltage (V)	(480Y / 277 V AC) (96 V DC)
Standards	CSA 22.2 No. 5 IEC/EN 60947-2 UL 489
Tripping Characteristic	C