

Representative Image

# Alternate Catalog No. SU204M-K13
# Catalog No. 2CDS274337R0447

**Description: UL489 MCB 4P K 13A 480/277**

**UPC No 4016779930628**

**Home > Modular DIN Rail Products > Mini Circuit breakers**

SU204M-K13 Miniature Circuit Breaker K-Char., 10kA, 13A, 4P UL489

## Descriptors

| | |
|---|---|
| Category | Mini Circuit breakers |

## Specifications

| | |
|---|---|
| Interrupting Rating acc. to UL489 | (480Y / 277 V AC) 10 kA<br>(96 V DC) 10 kA |
| Number of Poles | 4 |
| Power Loss | 9,2 W<br>at Rated Operating Conditions per Pole 2,3 W |
| Product Main Type | SU200M |
| Rated Current | 13 A |
| Rated Ultimate Short-Circuit Breaking Capacity | (400 V AC) 15 kA |
| Rated Voltage (V) | (480Y / 277 V AC)<br>(96 V DC) |
| Standards | CSA 22.2 No. 5<br>IEC/EN 60947-2<br>UL 489 |
| Tripping Characteristic | K |