

**Alternate Catalog No. SU204M-K25**  
**Catalog No. 2CDS274337R0517**

**Description:** UL489 MCB 4P K 25A 480/277

**UPC No** 4016779930666

**Home > Modular DIN Rail Products > Mini Circuit breakers**

SU204M-K25 Miniature Circuit Breaker K-Char., 10kA, 25A, 4P UL489



Representative Image

**Descriptors**

Category	Mini Circuit breakers
----------	-----------------------

**Specifications**

Interrupting Rating acc. to UL489	(480Y / 277 V AC) 10 kA (96 V DC) 10 kA
Number of Poles	4
Power Loss	12,8 W at Rated Operating Conditions per Pole 3,2 W
Product Main Type	SU200M
Rated Current	25 A
Rated Ultimate Short-Circuit Breaking Capacity	(400 V AC) 15 kA
Rated Voltage (V)	(480Y / 277 V AC) (96 V DC)
Standards	CSA 22.2 No. 5 IEC/EN 60947-2 UL 489
Tripping Characteristic	K