



Representative Image

**Alternate Catalog No. SU204M-Z60**  
**Catalog No. 2CDS274337R0588**

**Description: UL489 MCB 4P Z 60A 240**

**UPC No 4016779933742**

**Home > Modular DIN Rail Products > Mini Circuit breakers**

SU204M-Z60 Miniature Circuit Breaker Z-Char., 10kA, 60A, 4P UL489

**Descriptors**

Category | Mini Circuit breakers

**Specifications**

Interrupting Rating acc. to UL489	(240 V AC) 10 kA (96 V DC) 10 kA
Number of Poles	4
Power Loss	19,6 W at Rated Operating Conditions per Pole 4,9 W
Product Main Type	SU200M
Rated Current	60 A
Rated Ultimate Short-Circuit Breaking Capacity	(400 V AC) 15 kA
Rated Voltage (V)	(240 V AC) (96 V DC)
Standards	CSA 22.2 No. 5 IEC/EN 60947-2 UL 489
Tripping Characteristic	Z