



**Alternate Catalog No. SU204MR-K0.3**  
**Catalog No. 2CDS274347R0117**

**Description:** MCB SU200MR RTT 4P K 0.3A BCP

**UPC No** 4016779959193

**Home > Modular DIN Rail Products > Mini Circuit breakers**

SU204MR-K0.3 MCB K-Char., 10kA, 0.3A, 4P, RTT UL 489, Ring Cable Lug

**Descriptors**

Category	Mini Circuit breakers
----------	-----------------------

**Specifications**

Interrupting Rating acc. to UL489	(480Y / 277 V AC) 10 kA (96 V DC) 10 kA
Number of Poles	4
Power Loss	at Rated Operating Conditions per Pole 1.7 W
Product Main Type	SU200MR
Rated Current	0.30 A
Rated Voltage (V)	(480Y / 277 V AC) (96 V DC)
Tripping Characteristic	K