

Alternate Catalog No. SU204MR-K8
Catalog No. 2CDS274347R0407

Description: MCB SU200MR RTT 4P K 8A BCP

UPC No 4016779959391

Home > Modular DIN Rail Products > Mini Circuit breakers

SU204MR-K8 MCB K-Char., 10kA, 8A, 4P, RTT UL 489, Ring Cable Lug

Descriptors

Category	Mini Circuit breakers

Specifications

Interrupting Rating acc. to UL489	(480Y / 277 V AC) 10 kA (96 V DC) 10 kA
Number of Poles	4
Power Loss	at Rated Operating Conditions per Pole 1.5 W
Product Main Type	SU200MR
Rated Current	8 A
Rated Voltage (V)	(480Y / 277 V AC) (96 V DC)
Tripping Characteristic	K