



Representative Image

**Alternate Catalog No. SU204MR-K10**  
**Catalog No. 2CDS274347R0427**

**Description:** MCB SU200MR RTT 4P K 10A BCP

**UPC No 4016779959414**

**Home > Modular DIN Rail Products > Mini Circuit breakers**

SU204MR-K10 MCB K-Char., 10kA, 10A, 4P, RTT UL 489, Ring Cable Lug

**Descriptors**

|          |                       |
|----------|-----------------------|
| Category | Mini Circuit breakers |
|----------|-----------------------|

**Specifications**

|                                   |                                              |
|-----------------------------------|----------------------------------------------|
| Interrupting Rating acc. to UL489 | (480Y / 277 V AC) 10 kA<br>(96 V DC) 10 kA   |
| Number of Poles                   | 4                                            |
| Power Loss                        | at Rated Operating Conditions per Pole 2.1 W |
| Product Main Type                 | SU200MR                                      |
| Rated Current                     | 10 A                                         |
| Rated Voltage (V)                 | (480Y / 277 V AC)<br>(96 V DC)               |
| Tripping Characteristic           | K                                            |