

## Alternate Catalog No. SU204MR-K32
## Catalog No. 2CDS274347R0537

**Description: MCB SU200MR RTT 4P K 32A BCP**

**UPC No 4016779959551**

**Home > Modular DIN Rail Products > Mini Circuit breakers**

SU204MR-K32 MCB K-Char., 10kA, 32A, 4P, RTT UL 489, Ring Cable Lug

### Descriptors

| | |
|---|---|
| Category | Mini Circuit breakers |

### Specifications

| | |
|---|---|
| Interrupting Rating acc. to UL489 | (480Y / 277 V AC) 10 kA<br>(96 V DC) 10 kA |
| Number of Poles | 4 |
| Power Loss | at Rated Operating Conditions per Pole 3.7 W |
| Product Main Type | SU200MR |
| Rated Current | 32 A |
| Rated Voltage (V) | (480Y / 277 V AC)<br>(96 V DC) |
| Tripping Characteristic | K |