

Representative Image

Alternate Catalog No. SU204MR-K50
Catalog No. 2CDS274347R0577

Description: MCB SU200MR RTT 4P K 50A BCP

UPC No 4016779959612

Home > Modular DIN Rail Products > Mini Circuit breakers

SU204MR-K50 MCB K-Char., 10kA, 50A, 4P, RTT UL 489, Ring Cable Lug

Descriptors

Category	Mini Circuit breakers

Specifications

Interrupting Rating acc. to UL489	(240 V AC) 10 kA (96 V DC) 10 kA
Number of Poles	4
Power Loss	at Rated Operating Conditions per Pole 4.5 W
Product Main Type	SU200MR
Rated Current	50 A
Rated Voltage (V)	(240 V AC) (96 V DC)
Tripping Characteristic	K