



Alternate Catalog No. S204MR-K40
Catalog No. 2CDS274437R0557

Description: MCB - S200 - 1P - D - 6 A

UPC No 4016779960090

Home > Modular DIN Rail Products > Mini Circuit breakers

S204MR-K40 MCB K-Char., 10kA, 40A, 4P, RTT UL 1077, Ring Cable Lug

Descriptors

| | |
|----------|-----------------------|
| Category | Mini Circuit breakers |
|----------|-----------------------|

Specifications

| | |
|------------------------------------|--|
| Interrupting Rating acc. to UL1077 | (208Y / 120 V AC) 10 kA (240 V AC) 10 kA |
| Number of Poles | 4 |
| Product Main Type | S200MR |
| Rated Current | 40 A |
| Rated Voltage (V) | (208Y / 120 V AC) (240 V AC) (480Y / 277 V AC) |
| Tripping Characteristic | K |