

**Alternate Catalog No. F204A-40/0.03 110V
Catalog No. 2CSF204199R1400**

Description: F204 40A 30MA 110V PB TEST VOLTAGE

UPC No 8012542342830

Home > Modular DIN Rail Products > Residual current devices

The RCCBs F200 series assures protection against the effects of sinusoidal alternating and direct pulsating earth fault currents, protection, against indirects contacts and additional protection against direct (with sensitivity = 30 mA) contacts. Applications: residential, commercial, industrial. This particular series has the minimum operating voltage of test bottom of 110V and it is suitable for application at 230V.



Representative Image

Descriptors

Category	Residual current devices
----------	--------------------------

Specifications

Number of Poles	4
Product Main Type	F200
Rated Current	40 A
Rated Operational Voltage	480Y/277 V AC
Rated Residual Current	30 mA
Standards	IEC 61008 UL 1053
Type of Residual Current	A type