



Representative Image

Catalog No. 2TLA010051R0100
Description: SENTRY SSR20M 85-265 VAC/DC
UPC No 7350024483314
Home > Machine Safety > Safety Relays

Safety relay with relay outputs 3NO+1NC, 85-265 VAC/120-375 VDC supply voltage and screw terminals. For monitoring of two-hand devices. Manual or automatic reset selectable by switch on front.

Descriptors

Category	Safety Relays
----------	---------------

Specifications

Supply Voltage	85-265VAC/120-375VDC
Monitoring of Emergency Stops	No
Safe Output Expansion	No
Monitoring of Gate Switches	No
Monitoring OSSD Devices (ex. Light Curtains)	No
Two Hand Control	Yes
Safety Mats/Edges and Bumpers	No
Timer Function	No
Outputs	Failsafe (Relay) 3 NO + 1 NC
Product Class	Sentry Safety Relays
Product Main Type	SSR
Degree of Protection	IP20

Classifications

ETIM 8 (Etim8)	EC001452 - Two-hand control relay
ETIM 7	EC001452 - Two-hand control relay

Dimensions

Product Net Height	120 mm
Product Net Width	22.5 mm
Product Net Weight	0.214kg
Product Net Depth / Length	120 mm

Safety Information

Performance Level	Up to e
-------------------	---------