

## Alternate Catalog No. X75-B4-48-ND Catalog No. 3AUA0000224502

**Description: PSTX ENCLOSED 75HP 480V TYPE4 ND**

**UPC No 6438177513964**

**Home > Soft Starters > Softstarter - Enclosed (PSTX)**

PSTX normal duty enclosed softstarters are the ultimate softstarting solution. Includes all features of the PSTX normal duty, sized for normal duty applications. Both the PSTX softstarter and TMAX XT breakers are utilized. Door mounted pilot devices include PSTX keypad, hand-off-auto selector switch, start and stop pushbuttons, power on pilot light, run pilot light and fault pilot light. Good for Normal Duty class 10 starts for 75HP104A, heavy duty class 30 starts for 50HP/68A, SSCR rating of 65kA, 480V and type 4 enclosure.



Representative Image

### Descriptors

Category	Softstarter - Enclosed (PSTX)
----------	-------------------------------

### Specifications

Enclosure Type	NEMA 4
Motor Voltage	480 V
Normal Duty: Motor Power (HP) at 460V	75
Heavy Duty: Output Current (A)	80
Protection Type	Circuit Breaker
Power Dissipation In Watts	20
Height (Inches)	24
Width (Inches)	20
Depth (Inches)	12

### Dimensions

Weight (lb)	78
Height (mm)	609,6
Width (mm)	508
Depth (mm)	304,8
Weight (kg)	35