



Alternate Catalog No. X150-B4-48-ND
Catalog No. 3AUA0000224505

Description: PSTX ENCLOSED 150HP 480V TYPE4 ND

UPC No 6438177513995

Home > Soft Starters > Softstarter - Enclosed (PSTX)

PSTX normal duty enclosed softstarters are the ultimate softstarting solution. Includes all features of the PSTX normal duty, sized for normal duty applications. Both the PSTX softstarter and TMAX XT breakers are utilized. Door mounted pilot devices include PSTX keypad, hand-off-auto selector switch, start and stop pushbuttons, power on pilot light, run pilot light and fault pilot light. Good for Normal Duty class 10 starts for 150HP/192A, heavy duty class 30 starts for 125HP/169A, SSCR rating of 65kA, 480V and type 4 enclosure.

Descriptors

Category	Softstarter - Enclosed (PSTX)
----------	-------------------------------

Specifications

Enclosure Type	NEMA 4
Motor Voltage	480 V
Normal Duty: Motor Power (HP) at 460V	150
Heavy Duty: Output Current (A)	169
Protection Type	Circuit Breaker
Power Dissipation In Watts	90
Height (Inches)	48
Width (Inches)	36
Depth (Inches)	16

Dimensions

Weight (lb)	280
Height (mm)	1219,2
Depth (mm)	406,4
Weight (kg)	127