

Alternate Catalog No. X300-B4-48-ND Catalog No. 3AUA0000224508

Description: PSTX ENCLOSED 300HP 480V TYPE4 ND

UPC No 6438177514022

Home > Soft Starters > Softstarter - Enclosed (PSTX)

PSTX normal duty enclosed softstarters are the ultimate softstarting solution. Includes all features of the PSTX normal duty, sized for normal duty applications. Both the PSTX softstarter and TMAX XT breakers are utilized. Door mounted pilot devices include PSTX keypad, hand-off-auto selector switch, start and stop pushbuttons, power on pilot light, run pilot light and fault pilot light. Good for Normal Duty class 10 starts for 300HP/361A, heavy duty class 30 starts for 250HP/302A, SSCR rating of 65kA, 480V and type 4 enclosure.



Descriptors

| | |
|----------|-------------------------------|
| Category | Softstarter - Enclosed (PSTX) |
|----------|-------------------------------|

Specifications

| | |
|---------------------------------------|-----------------|
| Enclosure Type | NEMA 4 |
| Motor Voltage | 480 V |
| Normal Duty: Motor Power (HP) at 460V | 300 |
| Heavy Duty: Output Current (A) | 302 |
| Protection Type | Circuit Breaker |
| Power Dissipation In Watts | 260 |
| Height (Inches) | 48 |
| Width (Inches) | 36 |
| Depth (Inches) | 16 |

Dimensions

| | |
|-------------|--------|
| Weight (lb) | 300 |
| Height (mm) | 1219,2 |
| Depth (mm) | 406,4 |
| Weight (kg) | 136 |