

## Alternate Catalog No. X700-B4-48-ND Catalog No. 3AUA0000224512

**Description: PSTX ENCLOSED 700HP 480V TYPE4 ND**

**UPC No 6438177514060**

**Home > Soft Starters > Softstarter - Enclosed (PSTX)**

PSTX normal duty enclosed softstarters are the ultimate softstarting solution. Includes all features of the PSTX normal duty, sized for normal duty applications. Both the PSTX softstarter and TMAX XT breakers are utilized. Door mounted pilot devices include PSTX keypad, hand-off-auto selector switch, start and stop pushbuttons, power on pilot light, run pilot light and fault pilot light. Good for Normal Duty class 10 starts for 700HP/840A, heavy duty class 30 starts for 600HP/720A, SSCR rating of 65kA, 480V and type 4 enclosure.



Representative Image

### Descriptors

|          |                               |
|----------|-------------------------------|
| Category | Softstarter - Enclosed (PSTX) |
|----------|-------------------------------|

### Specifications

|                                       |                 |
|---------------------------------------|-----------------|
| Enclosure Type                        | NEMA 4          |
| Motor Voltage                         | 480 V           |
| Normal Duty: Motor Power (HP) at 460V | 700             |
| Heavy Duty: Output Current (A)        | 720             |
| Protection Type                       | Circuit Breaker |
| Power Dissipation In Watts            | 216             |
| Height (Inches)                       | 72              |
| Width (Inches)                        | 36              |
| Depth (Inches)                        | 24              |

### Dimensions

|             |       |
|-------------|-------|
| Weight (lb) | 770   |
| Height (mm) | 2286  |
| Depth (mm)  | 609,6 |
| Weight (kg) | 349   |