

Alternate Catalog No. X900-F4-48-ND Catalog No. 3AUA0000224513

Description: PSTX ENCLOSED 900HP 480V TYPE4 ND

UPC No 6438177514077

Home > Soft Starters > Softstarter - Enclosed (PSTX)

PSTX normal duty enclosed softstarters are the ultimate softstarting solution. Includes all features of the PSTX normal duty, sized for normal duty applications. Both the PSTX softstarter and TMAX XT breakers are utilized. Door mounted pilot devices include PSTX keypad, hand-off-auto selector switch, start and stop pushbuttons, power on pilot light, run pilot light and fault pilot light. Good for Normal Duty class 10 starts for 900HP/1062A, heavy duty class 30 starts for 800HP/840A, SSCR rating of 65kA, 480V and type 4 enclosure.



Descriptors

Category	Softstarter - Enclosed (PSTX)
----------	-------------------------------

Specifications

Motor Voltage	460 V
Normal Duty: Motor Power (HP) at 460V	900
Heavy Duty: Output Current (A)	840
Protection Type	Fuse Disconnect
Power Dissipation In Watts	510
Height (Inches)	72
Width (Inches)	72
Depth (Inches)	24

Dimensions

Weight (lb)	1353
Height (mm)	1828,8
Depth (mm)	609,6
Weight (kg)	614