

## Alternate Catalog No. X50-B4-48-XD Catalog No. 3AUA0000226360

**Description: PSTX ENCLOSED 50HP 480V TYPE4 XD**

**UPC No 6438177522379**

**Home > Soft Starters > Softstarter - Enclosed (PSTX)**

PSTX extreme duty enclosed softstarters are the ultimate softstarting solution. Includes all features of the PSTX normal duty, sized for heavy duty applications, plus an AC-3 emergency bypass. Both the PSTX softstarter and TMAX XT breakers are utilized. Door mounted pilot devices include PSTX keypad, hand-off-auto selector switch, start and stop pushbuttons, power on pilot light, run pilot light, fault pilot light, normal/emergency bypass selector switch, emergency bypass start and stop pushbuttons and emergency bypass pilot light. Good for Normal Duty class 10 starts for 60HP/80A, heavy duty class 30 starts for 50HP/68A, SSCR rating of 65kA, 480V and type 4 enclosure.



Representative Image

### Descriptors

Category	Softstarter - Enclosed (PSTX)
----------	-------------------------------

### Specifications

Enclosure Type	NEMA 4
Motor Voltage	480 V
Motor HP at 460V- Extreme duty	50
Protection Type	Circuit Breaker
Power Dissipation In Watts	20
Height (Inches)	24
Width (Inches)	20
Depth (Inches)	12

### Dimensions

Weight (lb)	88
Height (mm)	609,6
Width (mm)	508
Depth (mm)	304,8
Weight (kg)	40