

Alternate Catalog No. X125-B4-48-XD Catalog No. 3AUA0000226363

Description: PSTX ENCLOSED 125HP 480V TYPE4 XD

UPC No 662348099520

Home > Soft Starters > Softstarter - Enclosed (PSTX)

PSTX extreme duty enclosed softstarters are the ultimate softstarting solution. Includes all features of the PSTX normal duty, sized for heavy duty applications, plus an AC-3 emergency bypass. Both the PSTX softstarter and TMAX XT breakers are utilized. Door mounted pilot devices include PSTX keypad, hand-off-auto selector switch, start and stop pushbuttons, power on pilot light, run pilot light, fault pilot light, normal/emergency bypass selector switch, emergency bypass start and stop pushbuttons and emergency bypass pilot light. Good for Normal Duty class 10 starts for 150HP/192A, heavy duty class 30 starts for 125HP/169A, SSCR rating of 65kA, 480V and type 4 enclosure.



Representative Image

Descriptors

| | |
|----------|-------------------------------|
| Category | Softstarter - Enclosed (PSTX) |
|----------|-------------------------------|

Specifications

| | |
|--------------------------------|-----------------|
| Enclosure Type | NEMA 4 |
| Motor Voltage | 480 V |
| Motor HP at 460V- Extreme duty | 125 |
| Protection Type | Circuit Breaker |
| Power Dissipation In Watts | 90 |
| Height (Inches) | 48 |
| Width (Inches) | 36 |
| Depth (Inches) | 16 |

Dimensions

| | |
|-------------|--------|
| Weight (lb) | 284 |
| Height (mm) | 1219,2 |
| Depth (mm) | 406,4 |
| Weight (kg) | 129 |