



**Alternate Catalog No. X150-B4-48-XD**  
**Catalog No. 3AUA0000226364**

**Description: PSTX ENCLOSED 150HP 480V TYPE4 XD**

**UPC No 6438177522416**

**Home > Soft Starters > Softstarter - Enclosed (PSTX)**

PSTX extreme duty enclosed softstarters are the ultimate softstarting solution. Includes all features of the PSTX normal duty, sized for heavy duty applications, plus an AC-3 emergency bypass. Both the PSTX softstarter and TMAX XT breakers are utilized. Door mounted pilot devices include PSTX keypad, hand-off-auto selector switch, start and stop pushbuttons, power on pilot light, run pilot light, fault pilot light, normal/emergency bypass selector switch, emergency bypass start and stop pushbuttons and emergency bypass pilot light. Good for Normal Duty class 10 starts for 200HP/248A, heavy duty class 30 starts for 150HP/192A, SSCR rating of 65kA, 480V and type 4 enclosure.

**Descriptors**

Category	Softstarter - Enclosed (PSTX)
----------	-------------------------------

**Specifications**

Enclosure Type	NEMA 4
Motor Voltage	480 V
Motor HP at 460V- Extreme duty	150
Protection Type	Circuit Breaker
Power Dissipation In Watts	140
Height (Inches)	48
Width (Inches)	36
Depth (Inches)	16

**Dimensions**

Weight (lb)	284
Height (mm)	1219,2
Depth (mm)	406,4
Weight (kg)	129