

## Alternate Catalog No. X600-B4-48-XD Catalog No. 3AUA0000228980

**Description: PSTX ENCLOSED 600HP 480V TYPE4 XD**

**UPC No 662348099537**

**Home > Soft Starters > Softstarter - Enclosed (PSTX)**

PSTX extreme duty enclosed softstarters are the ultimate softstarting solution. Includes all features of the PSTX normal duty, sized for heavy duty applications, plus an AC-3 emergency bypass. Both the PSTX softstarter and TMAX XT breakers are utilized. Door mounted pilot devices include PSTX keypad, hand-off-auto selector switch, start and stop pushbuttons, power on pilot light, run pilot light, fault pilot light, normal/emergency bypass selector switch, emergency bypass start and stop pushbuttons and emergency bypass pilot light. Good for Normal Duty class 10 starts for 700HP/840A, heavy duty class 30 starts for 600HP/720A, SSCR rating of 65kA, 480V and type 4 enclosure.



### Descriptors

Category	Softstarter - Enclosed (PSTX)
----------	-------------------------------

### Specifications

Enclosure Type	NEMA 4
Motor Voltage	480 V
Motor HP at 460V- Extreme duty	600
Protection Type	Circuit Breaker
Power Dissipation In Watts	216
Height (Inches)	85
Width (Inches)	36
Depth (Inches)	24

### Dimensions

Weight (lb)	1413
Height (mm)	1828,8
Depth (mm)	609,6
Weight (kg)	641