



Representative Image

Catalog No. 500-G

Description: BEAM CLAMP, JAW OPENING 15/16IN GRY

UPC No 704508436605

Home > Cable Protection Systems > Ocal > Beam clamps

PVC Coated Hanger Rod Beam Clamp, Jaw Opening 15/16 Inch/23.81 Millimeters, Load Rating 450 Pounds/204.12 Kilograms, Base 1 Inch x 1-1/4 Inch, Malleable Iron, Gray

Descriptors

Category	Beam clamps
Special Features	PVC Coating for Corrosion Protection
Application	Used to Support and Attach Conduit Runs to Structural Beams

Specifications

Material	Malleable Iron
Maximum Load	450 pounds , 204.12 kg
Maximum Jaw Opening	15/16 in , 23.81 mm
Finish	PVC Coated
Color	Gray

Classifications

Brand Name	Ocal
Standard	CSA LR-52208

Dimensions

Size	1 x 1-1/4 Inch
------	----------------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000464 Fixing clamp
Type of fastening	Screwing
Connection type construction part	Other
Tube/cable diameter	23.81-23.81 mm

by ABB

ETIM	EC000464 Fixing clamp
Hinging	N
Material	Other
Surface protection	Coated