



Catalog No. 54822BE

Description: CU TP 2HL LUG LONG BRL 400 1/4B BLU

UPC No 786210194752

Home > Connectivity & Grounding > Color Keyed / Blackburn > Cable or wire lug

Copper Two-Hole Lug, Long Barrel, Blind End, Max 35KV, Wire Size 400 kcmil, 1/4 Inch Bolt Size, 3/4 Inch Hole Spacing, Tin Plated, Die Code 76, Die Color Code Blue

Descriptors

Category	Cable or wire lug
----------	-------------------

Specifications

Cable Size	400 kcmil
Number Of Holes	2
Voltage Rating	35 kV
Insulation	None
Material	Copper
Color	Blue

Classifications

Brand Name	Color Keyed / Blackburn
Standard	UL E9809

Dimensions

Stud Size	1/4 in
-----------	--------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	180° (horizontal)
Slender flange model	N
Insulated	N
With sight-hole	N



ETIM	EC001051 Tube cable lug for copper conductors
Material	Copper
Surface protection	Tinned
Number of mounting holes	2
AWG size	400 kcmil

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	4503	622302	N/A	1097195_2015-02-20	N/A
CSA	7222	622302	N/A	LR7222-164-FIG1	N/A
UL	E9809	N/A	ZMVV	N/A	N/A