

Catalog No. 9T10A1006G02

Description: 3A,150KVA,480-208Y,150C,N2,K1,-3DB,DOE

UPC No 783173901403

Home > Transformers > Dry Type Vented > Low Noise

ABB's Low-Noise Low-Voltage General Purpose Dry-Type transformers also come in variants that allow for lower than standard (NEMA ST-20) audible noise levels and are UL Listed. Ideally suited for installations where a transformers inherent audible noise needs to be as low as possible. They are available with either a -3dB or -5dB levels of noise reduction. Our Type QL & QF low-noise transformers meet DOE 2016 efficiency standards and are UL Energy Verified as energy efficient. They are available with aluminum or copper windings and in all three temperature rise ratings. Core and coil assemblies are mounted on rubber isolation pads to reduce noise. Single-piece front/back is easily removable for installation and service. Qualified to the seismic requirements of IEEE-693-2005 and IBC-2021 and CBC 2022.



Representative Image

Descriptors

Category	Low Noise
----------	-----------

Specifications

TransType	DOE 2016
Phase	3
PriVoltage	480
SecVoltage	208Y/120
KVA	150 KVA
Coil Material	AL
TempRise	150 °C
Frequency	60 Hz
AmbTemp	40 °C
EnergyEfficiency	DOE 2016
KFactor	K1
Enclosure Type	NEMA 2
Sound	-3dB

Classifications

UL	Yes
----	-----