



Catalog No. 9T10C1342G31

Description: 3C,30KVA,208-480Y,115C,N2,K1,DOE

UPC No 783173906934

Home > Transformers > Dry Type Vented > General Purpose

ABB Low-Voltage General Purpose Dry-Type transformers are built to last more than 20 years and are UL Listed. Our Type QL & QF transformers meet DOE 2016 efficiency standards and are UL Energy Verified as energy efficient. They are available with aluminum or copper windings and in all three temperature rise ratings. Quiet Performance-Core and coil assemblies are mounted on rubber isolation pads to reduce noise. Single-piece front/back is easily removable for installation and service. Qualified to the seismic requirements of IEEE-693-2005 and IBC-2021 and CBC 2022.

Descriptors

Category	General Purpose
----------	-----------------

Specifications

TransType	QL
Phase	3
PriVoltage	208
SecVoltage	480Y/277
KVA	30 KVA
Coil Material	CU
TempRise	115 °C
Frequency	60 Hz
AmbTemp	40 °C
EnergyEfficiency	DOE 2016
KFactor	K1
Enclosure Type	NEMA 2
Sound	Std

Classifications

UL	Yes
----	-----

