



**Catalog No. 9T21B1002G02**

**Description: 1A,7.5kVA,120x240-120/240,115C,3R,QMS**

**UPC No 783173004005**

**Home > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA**

ABB's QMS single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

**Descriptors**

Category	Single-Phase: .050kVA-3kVA and 5kVA-25kVA
GO Schedule	T7

**Specifications**

Phase	1
PriVoltage	120x240
SecVoltage	120/240
KVA	7.5 KVA
Coil Material	AL
TempRise	115 °C
ElecShield	N
Sub Type	Standard
Frequency	60 Hz
FrameSize	16600
TempClass	180 °C
AmbTemp	40 °C
InsulSys	IS-12
KFactor	K1
Enclosure Type	NEMA 3R

**Classifications**

UL	Yes
cUL	Yes