



**Catalog No. 9T21B9113**

**Description: 1A,15kVA,600-120/240,115C,3R,-2 4.8%,QMS**

**UPC No 783173001295**

**Home > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA**

ABB's QMS single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

**Descriptors**

Category	Single-Phase: .050kVA-3kVA and 5kVA-25kVA
GO Schedule	T7

**Specifications**

Phase	1
PriVoltage	600
SecVoltage	120/240
KVA	15 KVA
Coil Material	AL
TempRise	115 °C
ElecShield	N
Sub Type	Buck Boost Autotransformer
Frequency	60 Hz
FrameSize	19500
TempClass	180 °C
AmbTemp	40 °C
InsulSys	IS-12
KFactor	K1
Enclosure Type	NEMA 3R

**Classifications**

UL	Yes
cUL	Yes